

### **Ihr zuverlässiger Spezialist für qualitativ hochwertige Tieflochbohrungen und seitliche Bearbeitungen**

Das HASCO Special Machining Center SMC ist Ihr zuverlässiger Partner für qualitativ hochwertige Tieflochbohrungen und die seitliche Bearbeitung. Auf modernsten Tieflochbohrzentren fertigen wir schnell und zuverlässig hochpräzise Tieflochbohrungen, auf Wunsch zusätzlich auch mit Anschlussgewinden, Beschriftungen und seitlichen Bearbeitungen.

#### **Ihre Vorteile**

- Höchste Fertigungsqualität für leistungsstarke Formen und Werkzeuge
- Nutzenbringende Synergien aus Fremd- und Eigenfertigung
- Kürzeste und verlässliche Lieferzeiten ermöglichen planbare Prozesse

#### **Unsere Fertigungsschwerpunkte**


- Kühlbohrungen
- Bohrungen für Heizpatronen
- Bohrungen für Thermofühler
- Bohrungen für Hydraulikleitungen
- Seitliche Komplettbearbeitung
- Anschlussgewinde
- Beschriftungen

#### **Unsere technischen Möglichkeiten**

- Bohrungsdurchmesser 4 - 32 mm
- Bohrungstiefe bis 1.000 mm pro Seite
- Plattengewicht bis 2.000 kg

#### **Ihre Anfragen**

Ihren persönlichen Ansprechpartner finden Sie unter: [www.hasco.com/kontakt](http://www.hasco.com/kontakt)



# HASCO<sup>®</sup>

*Enabling with System.*

## SMC

*Deep hole drilling*

### ***Your reliable specialist for high quality deep hole drilling and side machining***

The HASCO Special Machining Center SMC is your reliable partner for high quality deep hole drilling and side machining. With the use of most modern deep hole drilling centers we produce quickly and reliably high-precision deep holes, if required with connection threads, labeling and side machining.

#### ***Your benefits***

- Highest machining quality for high-performance moulds and tools
- Beneficial synergies with the combination of external and in-house production
- Shortest and reliable delivery time enables better planning

#### ***Our machining main focus***

- Cooling holes
- Holes for heating cartridges
- Holes for thermocouples
- Holes for hydraulic lines
- Complete side machining
- Connection threads
- Labeling

#### ***Our technical possibilities***

- Hole diameter 4 - 32 mm
- Drilling depth up to 1,000 mm per side
- Max. plate weight 2,000 kg

#### ***Your inquiries***

Your personal contact can be found at: [www.hasco.com/contact](http://www.hasco.com/contact)

